



# PRICE LIST

## INSTRUCTIONS FOR ORDERING PZM™ SYSTEMS

The variables to consider in writing your order for PZM™ systems are:

1. Dynamic range required.
2. Size of plate\* and color
3. Battery powered or phantom powered
4. With transformer or op amp
5. Box or tube power supply, plug or cord

\*The size of the plate has no acoustical function but is used for mounting the PZM™ to a large surface - large being 4'x4' or larger.

### DYNAMIC RANGE

There are two choices

1. The PZM™ 130

The PZM™ 130 is the best choice for normal speech use and other than the widest range, most dynamic music. Sound levels in excess of 130 dB will cause distortion.

2. The PZM™ 150

The PZM™ 150 is a wider range microphone (20 Hz to 25,000 Hz) and will not distort until the sound level exceeds 150 dB. The PZM™ 150 is a slightly smoother response unit but is 2 dB noisier than the PZM™ 130 which has a self-noise that is the equivalent of a sound level of 26 dB.

### SIZE AND COLOR OF PLATE AND PRICE

MODEL #	SIZE	COLOR			PRICE		* Contact Wahrenbrock Sound Associates for dealer information
		Black	Clear	Gold Anodized	Dealer*	Retail	
PZM-130 Model A	6"x9"	—	—	—		\$240.00	
PZM-130 Model B	5"x6"	—	—	—		240.00	
PZM-130 Model C	4"x5"	—	—	—		240.00	
PZM-130 Model D	2½"x2½"	—	—	—		240.00	
PZM-130 Model L	Lavalier	—	—	—		240.00	
PZM-130 Model CLP	4"x4"	—	—	—		240.00	
PZM-150 Model B	5"x6"	—	—	—		262.00	

The CLP model, D Model, and Lavalier come with 15' cable terminated in a switchcraft A3M connector. All others have connection on plate for standard microphone cable.

### BATTERY OR PHANTOM POWERED

Please specify if you wish battery B or phantom power P

### TRANSFORMER OR OP AMP ?

Please specify with transformer (a Deane Jensen design)    , or Op Amp    

### AVAILABLE POWER SUPPLIES

- BT - Battery with transformer
- PT - Phantom with transformer
- TPT - Phantom power with transformer housed in tube
- BPT - Battery and phantom powered with transformer
- PXT - Dual op amp, phantom powered

NOTE: If you have need of a special version of the PZM™, ask for a quotation.

NOTE: The PZM™ 150 uses Bipolar power supply, BT, PT, and TPT.

### SAMPLE ORDERS

Quantity 2, Model PZM™ 150, Plate B, Color Gold with PT power supply  
Quantity 1, Model PZM™ 130, Plate CLP, Color Clear with BT power supply (note CLP specifies size)

Contact us if you have questions not answered by this instruction sheet. Be sure you have checked off each point on the check list.

NOTE: This price list supersedes previous price list. All prices subject to change without notice.

October 1, 1979 MAIL ORDERS- TO:

(213) 861-0397

WAHRENBROCK SOUND ASSOCIATES, LTD

ME 45  
See order slip

